# **MEMBRAPOR**

# SPECIFICATION SHEET FOR NO SENSOR TYPE NO/SF-100

#### PERFORMANCE CHARACTERISTICS

Nominal Range	0 – 100 ppm
Maximum Overload	ND
Inboard Filter	To remove effect of
	SO <sub>2</sub>
Expected Operation Life	3 years in air
Output Signal	550 ± 110 nA/ppm
Resolution	0,5 ppm
Temperature Range	- 20 °C to 45 °C
Pressure Range	Atmospheric ± 10%
Pressure Coefficient	No data
T <sub>90</sub> Response Time	< 25 sec
Relative Humidity Range	15 % to 90 % R.H.
	non-condensing
Typical Baseline Range (pure	+1 to + 4 ppm 1)
air, 20°C)	
Maximum Zero Shift (+20°C	12 ppm
to +40°C)	
Long Term Output Drift	< 2% signal loss/month
Recommended Load Resistor	10 Ohm
Bias Voltage	+ 300 mV
Repeatability	< 2 % of signal
Output Linearity	Linear

 $<sup>^{1)}</sup>$  Sensors not older then a few weeks show typical baseline values of  $\sim$  30 - 40 ppm after 12 h stabilisation in biassed operation. After two days the baseline stabilises to the specified value. Sensors older then a few month will stabilise faster.

#### **CROSS-SENSITIVITY DATA**

Interfering Gas	Cross-Sensitivity (%)
СО	0
SO <sub>2</sub>	0
H <sub>2</sub> S	0
NO <sub>2</sub>	~ 1
H <sub>2</sub>	0

Performance data conditions: 20 °C, 50% RH and 1013 mbar


## **APPLICATIONS**


Safety and Environmental Control

### PHYSICAL CHARACTERISTICS

Weight	~ 32 g
Position Sensitivity	None
Storage Life	Six months in
	container
Recommended Storage	5 °C – 20 °C
Temperature	
Warranty Period	12 months from date
	of dispatch

#### Standard-Size Outline Dimensions





The data contained in this document is for guidance only. Membrapor AG accepts no liability for any consequential losses, injury or damage resulting from the use of this document or the information contained within it. The data is given for guidance only. Customers should test under their own conditions, to ensure that the sensors are suitable for their own requirements.

REV.: 6/2004 Page 1 of 1

Phone: +41 43 311 72 00 Fax: +41 43 311 72 01 Email: info@membrapor.ch www.membrapor.ch MEMBRAPOR AG Rautistrasse 164 CH-8048 Zürich Switzerland